



The Mobility F.C. Membranes Company GmbH
A BWT Chemours Company

Technical Data Sheet – VM_Nafion® FC-815-RFG

VM_Nafion® FC-815-RFG

General

Membrane type: Perfluorinated cation-exchange membrane – reinforced and stabilized – thickness 15 µm, with low resistance, high mechanical stability, low dimensional swelling, and high stability in acidic environment.

Application: Fuel Cell application (H₂-PEMFC).

Membranes are identified by membrane type and identification number (Lot Number). Please refer to this type and identification number in case of queries. The experimental samples are labelled as VM (VM= Versuchsmuster in German language, in English Experimental Sample)

Delivery

The membrane is the transparent foil, delivered on a backing layer (multilayer PET foil). Carefully separate the membrane from the paper layers. The membrane is ready for use.

Handling

Keep membrane package closed / sealed when unused. Unpack membrane only for direct use and process it immediately after opening. Store, handle and process the membrane in a clean and dust-free area. Use only new and sharp knives or blades, when cutting the membrane.

Always wear protective gloves when handling the membrane. Handle with care, be sure not to puncture, crease or scratch the membrane, otherwise leaks will occur. All surfaces which may get into contact with the membrane during inspection, storage, pretreatment and mounting must be free of sharp edges or angles.

Pretreatment

The membrane does not need any pretreatment and is ready for use. Please assemble the membrane in dry form.

If you have any concerns about storage, chemical stability, and pretreatment please feel free to contact us for further information.

The Mobility F.C. Membranes Company GmbH
A BWT Chemours Company

Carl-Benz-Straße 4, 74321 Bietigheim-Bissingen, Germany
Phone: +49-(0)-7142-3737-900
Fax: +49-(0)-7142-3737-999
Email: info@fumatech.com



The Mobility F.C. Membranes Company GmbH
A BWT Chemours Company

Technical Data Sheet – VM_Nafion® FC-815-RFG

Physical and chemical data of VM_Nafion® FC-815-RFG

Nafion®	unit	FC-815-RFG
Membrane type		cation exchange membrane
Appearance		transparent / brown color
Backing foil		Multilayer PET
Reinforcement		Microporous one
H2O2-radical extinguisher additives		Rare earth and/or transition metal(s) and noble metal(s) based
Counter ion		H ⁺ form
Delivery form		dry
Thickness (dry)	µm	13 – 18
IEC (ion exchange capacity)	meq g ⁻¹	1.20 – 1.26
Conductivity in H ₂ O at T = 25 °C in H-form ^{a)}	mS cm ⁻¹	> 130
Young's modulus at 23 °C / 50 % r.h. ^{b)}	MPa	> 350
Yield strength at 23 °C / 50 % r.h. ^{b)}	MPa	> 30
Tensile strength at 23 °C / 50 % r.h. ^{b)}	MPa	> 30
Max swelling in X-Y after treatment at 100 °C/1hr in MD/TD ^{c)}	%	7,5 / 5,5
Version ^{d)}	1.0	Valid from Sept 25 th 2023

a) measured in four-electrode cell (in-plane)

b) determined by stress-strain measurement at T = 25 °C and 50 % r.h., according to DIN EN 527-1

c) treatment in DI water, no direct contact of sample with air during the treatment

d) changes without prior notices may apply.

Note: The product is not certified for drinking water applications. The data are not measured directly on the item supplied. The data sheet does not release the customer of the necessity of a goods inwards control procedure. All information included in this data sheet is based on tests and data believed to be reliable. The data do not imply any warranty or performance guarantee. It is the user's responsibility to examine performance, suitability and durability of the product for the intended purpose. The Mobility F.C. Membranes Company GmbH does not assume any liability for patent infringement resulting from the use of this product. Nafion® is a trademark of The Chemours Company (NYSE: CC) as of the date of issuing the TDS version.

Hereby, it is certified that all results of the measured item comply with the margins of the internal specification defined in the technical datasheet. All measurements and data recording are conducted in accordance with standardized procedures following the ISO 9001 certification.

The Mobility F.C. Membranes Company GmbH

A BWT Chemours Company

Carl-Benz-Straße 4, 74321 Bietigheim-Bissingen, Germany

Phone: +49-(0)-7142-3737-900

Fax: +49-(0)-7142-3737-999

Email: info@fumatech.com